

# Eaton 726016-12FD

Catalog Number: 726016-12FD

Eaton B-Line series ground mounted panel enclosure, 72" height, 16" length, 60" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series type 12 panel enclosures	726016-12FD
	<b>UPC</b>
	782051408102
<b>Product Length/Depth</b>	<b>Product Height</b>
16 in	72 in
<b>Product Width</b>	<b>Product Weight</b>
60 in	477.7 lb
<b>Certifications</b>	
UL 508A	
CSA C22.2.	
NEMA	

## Material/finish

### Material

Carbon steel

### Wall thickness

12 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Large double door

### Model

12FD enclosure

### Cover type

Hinged

### Mounting method

Ground

### Mounting hole details

Ground mount legs

### Locking provisions

Key lock padlock provision

### Closure type

Hinged

### Special features

Plated door clamps

## Standards

### NEMA Rating

12

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 726016-12FD](#)

# Eaton 726016-12FD

Catalog Number: 726016-12FD

Eaton B-Line series ground mounted panel enclosure, 72" height, 16" length, 60" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series type 12 panel enclosures	726016-12FD
	<b>UPC</b>
	782051408102
<b>Product Length/Depth</b>	<b>Product Height</b>
16 in	72 in
<b>Product Width</b>	<b>Product Weight</b>
60 in	477.7 lb
<b>Certifications</b>	
UL 508A	
CSA C22.2.	
NEMA	

## Material/finish

### Material

Carbon steel

### Wall thickness

12 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Large double door

### Model

12FD enclosure

### Cover type

Hinged

### Mounting method

Ground

### Mounting hole details

Ground mount legs

### Locking provisions

Key lock padlock provision

### Closure type

Hinged

### Special features

Plated door clamps

## Standards

### NEMA Rating

12

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 726016-12FD](#)