



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7802MD 30A 2P SNGL PH Ac Motor Disconnet

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 7802MD |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Motor Disconneter, 2 Poles, 30 A, 600 V Ac, 1.753 (L) X 1.825 (W) X 2.375 (H) In, Box Mount, -40 °C Operating Temperature, +75 °C Operating Temperature, Toggle Actuator, 0.31 LB |
| Weight per unit | 0.3100 (lbs/each) |
| Product Category | Misc Wiring Devices |

Features

| | |
|------------------|---|
| actuator | Toggle |
| amperage rating | 30 |
| connection | Side & Back Wired |
| load | 30A |
| operating cycles | 50,000 cycles minimum, resistive, inductive, tungsten filament lamp load (Fed Spec) |
| Poles | 2 |

Dimensions and Weight

| | |
|------|---|
| Size | 1.753" Depth x 1.825" Width x 2.375" Height |
|------|---|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | 30A 2P SNGL PH AC MOTOR DISCONNET |
| extra long description | P&S 7802MD 30A 2P SNGL PH AC MOTOR |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007267655 |
| Manufacturers Part Number | 7802MD |
| UPC | 785007267655 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | Manual Controller |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.31 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| environmental conditions | UL94 V2 |
| Frequency Rating | 60Hz |
| Mounting | BOX |
| Operating Temperature | Maximum continuous +75°C, minimum -40°C |
| standard | CSA Listed, UL Listed |