

## Features:



**Durable steel belt clip** for convenience.

**True zero feature** for accurate inside and outside measuring.

**Nylon-coated, hardened steel blade** resists abrasion and wear for long life.

**Multi-riveted end hook with bottom blade protector** reinforces the blade tip and provides maximum pull-out strength.

**Built-in shock absorber** to protect blade tip.

## Power-Return Steel Rules – Magnetic Dual-End Hook, Double-Sided Blade



918-25RE

### Additional Features:

- Large magnetic dual-end hook\* allows for easier one-person measurements on ferrous metals.\*\*
- Large dual-end hook with double-sided blade for easy measurements, markings, and drawings.
- Comfortable rubber grip built into case for positive gripping and impact resistance.
- Positive blade lock holds blade securely in place.
- Oversized easy-to-read blade numbers.
- Tape measure holders available.

Cat. No.	Blade Length	Width	Weight (lbs.)
918-16RE	16' (5 m)	1" (25 mm)	.60
918-25RE	25' (7.5 m)	1" (25 mm)	.90
918-7.5ME-RE	7.5 m (25')	25 mm (1")	.90
918-30RE	30' (9 m)	1" (25 mm)	1.10

\*Note: Patent pending design.

\*\*Note: Magnetic strength will vary with different types of metal surfaces.

## Power-Return Steel Rules – Magnetic Tip



916-25RE

### Additional Features:

- Rare Earth magnetic tip sticks to iron and steel surfaces for simple one-person measurements.
- Comfortable, non-slip rubber jacket for easy gripping of case.
- Thick rubber jacket protects case against fall impacts.
- Convenient two-step lock button – 1st step slows retraction of the blade; 2nd step holds the blade securely.
- High-visibility orange case for easy locating in work areas and tool bags.
- Oversized, bold black numbers (first 11 inches) for easy reading\*, 16" (406 mm) and 19" (485 mm) red stud markings.
- Tape measure holders available.

Cat. No.	Blade Length	Width	Weight (lbs.)
916-16RE	16' (5 m)	1" (25 mm)	.63
916-25RE	25' (7.5 m)	1" (25 mm)	.90
916-7.5ME-RE	7.5 m (25')	25 mm (1")	.90
916-30RE	30' (9 m)	1" (25 mm)	1.10

(Note: Magnetic strength will vary with different types of metal surfaces.)

\*Not available on Cat. No. 916-7.5ME-RE.

All dimensions are in inches and (millimeters) unless otherwise specified.

**▲WARNING:** Always wear approved eye protection.

**▲WARNING:** Protect hands when cleaning magnetic tip. Use gloves or cloth.

**▲WARNING:** Avoid magnetic contact with sensitive electronic or computer equipment.

**▲WARNING:** To avoid personal injury and damage to this tool, do not allow the tape blade to retract into case at full speed.

**▲WARNING:** NOT insulated. Do NOT use on live circuits.

**▲WARNING:** Do NOT open case. Spring motor is under tension, and opening case may cause injury.

