



Part Number: 8459

Audio/Control/Instrumentation, (25) 22 AWG (7x30) TC, PVC/PVC, CMG

[Request Sample](#)

Product Description

Twenty-five 22 AWG stranded (7x30) tinned copper conductors, conductors cabled, PVC insulation, PVC Jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	7x30	TC - Tinned Copper	25

Conductor Count:	25
Conductor Size:	22 AWG

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.011 in

Color Chart

Color
Black
White
Red
Green
Orange
Blue
White/Black
Red/Black
Green/Black
Orange/Black
Blue/Black
Black/White
Red/White
Green/White
Blue/White
Black/Red
White/Red
Orange/Red
Blue/Red
Red/Green
Orange/Green
Black/White/Red
White/Black/Red
Red/Black/White
Green/Black/White

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.387 in	0.04 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
15.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
34 pF/ft

Inductance

Nominal Inductance
0.17 μ H/ft

Current

Max. Recommended Current [A]
1.5 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS (CMG)
150 V RMS (UL AWM Style 2576)

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2576)
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	101 lbs/1000ft
Max Recommended Pulling Tension:	228 lbs
Min Bend Radius/Minor Axis:	4 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2576 (150 V 80°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
UL voltage rating:	300 V RMS (CMG)

Plenum/Non-Plenum

Plenum (Y/N): No

Part Number

Variants

Item #	Color	Footnote
8459 060100	Chrome	
8459 0601000	Chrome	C
8459 060500	Chrome	C
8459 0605000	Chrome	

Footnote: C - CRATE REEL PUT-UP.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.