



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636



A200M3CX A 200M3CX *Eaton Corp*

Catalog Number	A200M3CX
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, Non-Reversing Starter, 480V/60 HZ Coil Voltage, 90A, Three-Pole, Size 3, 25 HP At 208V, 30 HP At 240V, 50 HP At 480, 600V, A200 Series
Weight per unit	10.0 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

Poles	Three-pole
-------	------------

Dimensions and Weight

Depth	6.75
Height	4.63
Size	3
Width	6.63

Descriptions

Description	A 200M3CX
extra long description	ETN A200M3CX A 200M3CX
Features	All Class A200 non-reversing starters utilize Type B three-pole overload relays with optional Type A for auto reset applications. Sizes 5 and 6 include the needed current transformers. Moving and stationary contacts are front accessible for simple and easy inspection and maintenance. All Class A200 starters are UL listed and recognized and are CSA certified.
Long Description	Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 480V/60 Hz coil voltage, 90A, Three-pole, Size 3, 25 hp at 208V, 30 hp at 240V, 50 hp at 480,600V, A200 series
Product Type	A 200M3CX
Special Features	Bulk Package

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786678231297
Manufacturers Part Number	A200M3CX
UPC	786678231297

Taxonomies, Classifications, and Categories

Category Description	FULL VOLTAGE NON-REVERSING Control Starters
----------------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 9.95

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
..... Stationary Machinery and Equipment Outside Factory - Other
standard CSA Certified,UL Listed