

#### CWL1930P



#### CWL1930C





#### **CWL1930FO**

Dimensional Information: C-79 - C-82

Plug & Connector Specification Information:

Safety Grip L19-30: C-88 Severe Duty: C-97 Watertight: C-95

Receptacle Specification Information:

L19-30 : C-91 Watertight: C-96

Flanged Inlet & Flanged Outlet Specification Information:

L19-30 : C-93

# Hart-Lock<sup>™</sup> Industrial Specification Grade Locking Devices

4-Pole, 4-Wire Non-Grounding 30A, 3ØY 277/480V/AC NEMA L19-30





L19-30R

9-30R L19-30P

### 30A, 3ØY 277/480V NEMA L19-30

#### **Plugs & Connectors**

		Catalog No.			Certifications		ons	
Style & Description	Cord Dia.	Plug	Connector	4	<u></u>	Ē	<u> </u>	څ
Safety Grip™ Straight Body, Black & White	0.63-1.16" (15.9-29.4mm)	□ CWL1930P	□ CWL1930C	•			•	
Severe Duty, Yellow & Black	0.63-1.16" (15.9-29.4mm)	□ L1930PY	□ L1930CY	•			•	
Watertight, Yellow	0.43-1.15" (10.9-29.2mm)	□ L1930PW	□ L1930CW	•			•	
Watertight, All-Black	0.43-1.15" (10.9-29.2mm)	□ L1930PWBK	□ L1930CWBK	•			•	

#### **Receptacles**

	Catalog No.		Certification			
Style & Description	Single Receptacle	4	3	<u></u>	F(I)S	٨
Standard Industrial, Black	□ CWL1930R	•	•			
Watertight, Yellow	□ L1930RW	•		•		
Watertight, All-Black	□ L1930RWBK	•		•		

#### Flanged Inlets & Outlets

	Catalog No.			Certifications					
Style & Description	Flanged Inlet	Flanged Outlet	4	<b>3</b>	<u> </u>	F (I)	٨		
Standard Industrial, Black & White	□ CWL1930FI	_	•	•	•				
Standard Industrial, Black & White	_	□ CWL1930FO	•	•			•		

#### **Icon Key**

NAFTA Compliant - see page O-30

Accessories for NEMA L19-30 Locking Devices	
Description	Catalog No. 🌲
Neoprene weather protective boot for 30A 4-P, 4-W plug	□ BL1 •
Neoprene weather protective boot for 30A connector	□ BL2 •
Diecast aluminum single receptacle cover, vertical mount, for FS/FD boxes	□ 7420 •
Glass-filled nylon flanged inlet/outlet cover, vertical mount, for 30A devices	□ WP2 •









**COOPER** Wiring Devices

?

## Industrial Specification Grade 15A, 20A & 30A Locking Receptacles

2-Pole, 3-Wire Grounding; 3-Pole, 3-Wire Non-Grounding; 3-Pole, 4-Wire Grounding; 4-Pole, 4-Wire Non-Grounding; 4-Pole, 5-Wire Grounding

	Device Type	20A Hart-Lock™ Single Receptacles: NEMA L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, Non-NEMA 20A	30A Hart-Lock™ Single Receptacles: NEMA L5-30, L6-30, L7-30, L8-30, L9-30, L10-30, L11-30, L12-30, L13-30, L14-30, L15-30, L16-30, L17-30, L18-30, L19-30, L20-30, L21-30, L22-30, L23-30, Non-NEMA 30A	20A & 30A Hart-Lock™ Isolated Ground Single Receptacles: NEMA L5-20, L6-20, L7-20, L8-20, L5-30, L6-30, L7-30, L8-30, L14-20, L15-20, L16-20, L14-30, L15-30, L16-30, L21-20, L22-20, L23-20, L21-30, L22-30, L23-30	15A & 20A Hart-Lock <sup>™</sup> Receptacles, 2-Pole, 2-Wire: NEMA L1-15, L2-20	
	Wiring Type	Back & side wire	Back & side wire	Back & side wire	Back & side wire	
	Tallian 0 Oak	Listed to UL 498, file no. E2369     NEMA L5-20, L6-20, L7-20, L10-20, L14-20, L15-20, L18-20 & L21-20 also UL verified to Federal Spec. WC-596G	<ul> <li>Listed to UL 498, file no. E2369</li> <li>NEMA L5-30, L6-30, L7-30, L14-30, L15-30, L20-30, L21-30, L23-30 also UL verified to Federal Spec. WC-596G</li> </ul>	Listed to UL 498, file no. E2369      CSA certified to C22.2, no. 42 except NEMA L5-30		
	Testing & Code Compliance	CSA certified to C22.2, no.     42 except 7310B, NEMA     L11-20, L12-20, 7410B,     L18-20, L19-20, L20-20	CSA certified to C22.2, no.     42 except NEMA L11-20,     L12-20, 3330-2, L10-30,     L11-30, L12-30, L13-30,     3430, L18-30, L19-30, L20-30	NOM certified, except for L7-20, L8-20, L6-30, L7-30, L8-30, L16-20, L21-30, L22-30, L23-30	• Listed to UL 498, file no. E2369	
		NEMA L11-20, L14-20, L15-20, L18-20, L21-20, L22-20 also NOM certified	<ul> <li>NEMA L5-30, L10-30, L11-30, L14-30, L15-30, L18-30 also NOM certified</li> </ul>	LZZ-500, LZ5-500		
Specifications: Environmental	Flammability	Meets UL 94 requirements, V0 rated	Meets UL 94 requirements, V0 rated	Meets UL94 requirements, V0 rated	Meets UL94 requirements, V0 rated	
Specifi Enviror	Temperature Rating	-40°C to 60°C (-40°F to 140°F)	-40°C to 60°C (-40°F to 140°F)	-40°C to 70°C (-40°F to 158°F)	-40°C to 105°C (-40°F to 221°F)	
ns:	Dielectric Voltage	Withstands 2,500V per UL 498	Withstands 2,500V per UL 498	Withstands 2,500V per UL 498	Withstands 1500V per UL 498	
ecification Electrical	Current Interrupting	Yes, at full-rated current	Yes, at full-rated current	Yes, at full-rated current	Yes, at full-rated current	
Spe	Temperature Rise	Max. 30°C (86°F) after 200 cycles of overload @ 200% of rated current (DC)	Max. 30°C (86°F) after 200 cycles of overload @ 200% of rated current (DC)	Max. 30°C (86°F) after 200 cycles of overload @ 200% of rated current (DC)	Max. 30°C (86°F) after 100 cycles of overload @ 150% of rated current (DC)	
Specifications: Mechanical	Terminal Accommodation	#14 - #8 AWG	#14 - #8 AWG	#14 - #8 AWG	#14 - #10 AWG	
Specifi Mech	Voltage Ratings	Permanently marked on device	Permanently marked on device	Permanently marked on device	Permanently marked on device	
	Face	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon	
	Base	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon	
	Mounting Strap	.050" thick steel, zinc plated	.050" thick steel, zinc plated	.050" thick steel, zinc plated	.050" thick steel, zinc plated	
	Line Contacts	0.042" thick brass	0.042" thick brass	0.042" thick brass	0.032" thick brass, bronze	
Materials:	Terminal Screws	#10-32 brass, neutral screw nickel plated	#10-32 brass, neutral screw nickel plated	#10-32 brass, neutral screw nickel plated	#8-32 steel, nickel plated	
	Ground Screw	#10-32 brass (green)	#10-32 brass (green)	#10-32 brass (green)	#8-32 brass, green	
	Contact Springs	.040" thick brass	.040" thick brass	.040" thick brass	0.032" thick brass, bronze	
	Terminal Clamps/Plates	.040" thick brass	.040" thick brass	.040" thick brass	0.070" thick steel, zinc plated	
	Ground Contacts	.040" thick brass	.040" thick brass	.040" thick brass	N/A	
	Back Plate	.040" thick brass, nickel-plated	.040" thick brass, nickel-plated	.040" thick brass, nickel-plated	N/A	
	Mounting Screws	Steel, zinc-plated	Steel, zinc-plated	Steel, zinc-plated	Steel, zinc-plated	