



**SKU:** AK-6

**UPC:** 0783669008302

**Features & Benefits:**

**Description:** Aluminum Split Bolt, Main Range 6-10, Tap Range 6-10, Tin Plated, UL, CSA

## Specs

### Additional Class Attributes

Connection	Mechanical
Number of Conductors	1
Number of Poles	1

### Dimensions

Drive Size Main	3/4
Drive Type Main	External Hex
Height (IN)	0.56
Height BX (IN)	3.75
Length (IN)	1.38
Weight (LB)	0.0375
Weight BX (LB)	4.675
Width (IN)	0.75
Width BX (IN)	6

### Material and Finish

Conductor Material	Aluminum
Connector Finish	Tin
Insulation	NA
Material	Aluminum

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	NA
Wire Binding Torque	165

### General

Bag Quantity	1
--------------	---

<b>Carton Quantity Description</b>	STD PACK QTY 100
<b>Direct Burial</b>	No
<b>Dual Rated</b>	Yes
<b>NEMA Code</b>	S-588-4
<b>UPC Code</b>	78366900830

### Testing Standards

<b>CSA File Number</b>	72632
<b>CSA Standard</b>	C22.2 No. 65
<b>Prop65 Compliance</b>	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
<b>UL Control Number</b>	670B
<b>UL / CULUS Specification</b>	UL 486A/B Listed
<b>UL File Number</b>	E6207

### Environment and Temperature

<b>Temperature Rating</b>	90°C
---------------------------	------

### Color

<b>Color</b>	Silver
--------------	--------

### Conductor Ranges

<b>Conductor Range AL Solid (Secondary, tap, load)</b>	6 Sol - 10 Sol
<b>Conductor Range AL Stranded (Primary, run, main, line)</b>	6 Str - 10 Str
<b>Conductor Range AL Stranded (Secondary, tap, load)</b>	6 Str - 10 Str
<b>Conductor Range CU Solid (Primary, run, main, line)</b>	6 Sol - 10 Sol
<b>Conductor Range CU Solid (Secondary, tap, load)</b>	6 Sol - 10 Sol
<b>Conductor Range CU Stranded (Primary, run, main, line)</b>	6 Str - 10 Str
<b>Conductor Range CU Stranded (Secondary, tap, load)</b>	6 Str - 10 Str
<b>Conductor Range AL Solid (Primary, run, main, line)</b>	6 Sol - 10 Sol

### Voltage

<b>Voltage Rating</b>	35 kV
-----------------------	-------