



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## APS350 350 MCM Aluminum Split

*Nsi Industries*

Catalog Number	APS350
Manufacturer	Nsi Industries
Description	Aluminum Dual-Rated Split Bolt 2/0 STR - 350 MCM Aluminum Dual-Rated Split Bolts Are Made From Tin-Plated Aluminum. UI-486B Listed For Aluminum and Copper Conductor Combinations.
Weight per unit	0.4900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum Alloy-Tin Plated
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	2/0 STR - 350 MCM
Wire Type	Class A & B

### Material, Color, and Finish

Color	Aluminum
Finish	Aluminum

### Dimensions and Weight

Size	L=3.240 - W=1.500
------	-------------------

### Descriptions

Description	350 MCM ALUMINUM SPLIT
extra long description	NSI APS350 Aluminum Split Bolt 350
Features	Aluminum Dual-Rated Split Bolt 2/0 STR - 350 MCM Aluminum Dual-Rated Split bolts are made from tin-plated aluminum. UL-486B listed for aluminum and copper conductor combinations.
Long Description	Aluminum Dual-Rated Split Bolt 2/0 STR - 350 MCM Aluminum Dual-Rated Split bolts are made from tin-plated aluminum. UL-486B listed for aluminum and copper conductor combinations.
Product Type	Aluminum Split Bolt 350
Special Features	2/0 STR-350 MCM - 3 Pack



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381020567
Manufacturers Part Number	APS350
UPC	662381020567

## Taxonomies, Classifications, and Categories

Type	Aluminum Split Bolts
------	----------------------

## Packaging

Carton	1
Weight Per each	0.49

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C