ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818



# ASK1K1 (1)-2/0 to (1)-2/0 Power Dist Block

*Nsi Industries*

| | |
|---|---|
| Catalog Number | ASK1K1 |
| Manufacturer | Nsi Industries |
| Description | Power Distribution Block, 1 Primary Openings, 1 Secondary Openings, #14 to #2/0 Awg Primary Opening Wire Size, #14 to #2/0 Awg Secondary Opening Wire Size, 175 A, 600 V, Clear Acrylic, Maximum Of +90 °C, 2.9 In Overall Length, 1.04 In Overall Width, 2.34 In Overall Height, 0.58 LB |
| Weight per unit | 0.5800 (lbs/each) |
| Product Category | Power BLKS & Distribution BLKS |

## Features

| | |
|---|---|
| amperage rating | 175 Amps Per Pole |
| Number of Terminals | 2 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | (1) 2/0-14 AWG(LINE) - (1) 2/0-14 AWG(LOAD) |

## Material, Color, and Finish

| | |
|---|---|
| Color | Black |

## Dimensions and Weight

| | |
|---|---|
| Size | L=2.90 - H=2.34 - W=1.04 |

## Descriptions

| | |
|---|---|
| Description | (1)-2/0 TO (1)-2/0 POWER DIST BLOCK |
| extra long description | NSI AS-K1-K1 Pwr Dist 1x2/0-14Line |
| Features | Power Distribution Block (1) 2/0-14 AWG Primary (1) 2/0-14 AWG Secondary Power Distribution Blocks are made of high strength, high-conductivity aluminum alloy and are mounted in a high-strength glass-filled polyester base. Each block can stand alone or combine with other blocks to form a multi-block set. |
| Special Features | (1) 2/0-14 AWG (Line Side) - (1) 2/0-14 AWG (Load Side) - 175 Amps Per Pole |

## Manufacturer Information

| | |
|---|---|
| GTIN | 00662381166043 |
| UPC | 662381166043 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | TERMINAL BLOCKS POWER DIST BLOCKS |
| Type | Splicer/Reducer |

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 3 |
| Weight Per each | 0.58 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | NSI |
| Mounting | 2 Mounting Holes |
| standard | Recognized to UL1059 |