



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3507 N Van Buren Bypass
73701-0000, OK Enid
Phone: 580-701-6818
Fax: 580-234-5655



BR270H Type BR 2 Pole 70 Amp 240

Eaton Corp

Catalog Number	BR270H
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On High-Magnetic Circuit Breaker, High-Magnetic, 70 A, 10 Kaic, Two-Pole, 240V, BR, Common Breaker Trip, #8-1/0 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	0.5000 (lbs/each)
Product Category	2P Special Application Plug-In

Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	240 V - 240 V

Descriptions

Description	TYPE BR 2 POLE 70 AMP 240
extra long description	ETN BR270H TYPE BR 2 pole 70 amp 24
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on high-magnetic circuit breaker, High-magnetic, 70 A, 10 kAIC, Two-pole, 240V, BR, Common breaker trip, #8-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	Type BR 2 Pole 70 Amp 240V
Special Features	High-Magnetic

Manufacturer Information

Brand	Eaton
GTIN	00786676374705
Manufacturers Part Number	BR270H
UPC	786676374705

Taxonomies, Classifications, and Categories

Type	Thermal magnetic circuit breakers
------	-----------------------------------

Packaging

Carton	1
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3507 N Van Buren Bypass
73701-0000, OK Enid
Phone: 580-701-6818
Fax: 580-234-5655

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional Energy
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other Generation - Renewable Energy - Alternative
Energy Datacenters - IT Space: CI and Hyper Converged Other

standard

UL 489, Federal Specifications Classification W-C375