

Eaton BR612L125SDGP

Catalog Number: BR612L125SDGP

Eaton Eaton BR main lug loadcenter, Dual grounds, 125 A, 7, Aluminum, NEMA 1, Metallic, 10 kAIC, BR, Surface, NEMA 1, 12 Circuits, Twenty-four pole, 6 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #14-1 AWG Cu/Al

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR612L125SDGP
UPC	Product Length/Depth
786676002097	3.56 in
Product Height	Product Width
13 in	11 in
Product Weight	Warranty
12 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Gbk5 and gbk520 ground bars



defaultTaxonomyAttributeLabel

Special features

Dual grounds, current design

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Surface

Number of circuits

12

Number of spaces

6

Phase

Single-phase

Voltage rating

120/240V

Wire size

#14-1 AWG Cu/Al

Box size

7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Specifications and datasheets

[Eaton Specification Sheet - BR612L125SDGP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)