



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BJ2150 Type BJ BRKR 150A/2 Pole 120/240V 10K Req 4 Spaces *Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | BJ2150   |
| Manufacturer     | Eaton Corp   |
| Description      | Standard Trip Circuit Breaker, 150 A, Common Tripping Mechanism, Plug-On, 120/240 V Ac, 2.5 In Overall Height, 6.5 In Overall Length, 3.5 In Overall Width |
| Weight per unit  | 1.8 (lbs/each)   |
| Product Category | 2 Pole Standard Trip Plug-In   |

### Features

|            |                                   |
|------------|-----------------------------------|
| connection | Plug-on                           |
| dimensions | 6.5000 IN X 3.5000 IN X 2.5000 IN |
| Poles      | Two-pole                          |
| Trip Type  | Common                            |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | TYPE BJ BRKR 150A/2 POLE 120/240V 10K REQ 4 SPACES |
| extra long description | ETN BJ2150 BJ 150A/2 Pole 120/240V                 |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786676367103 |
| UPC  | 786676367103   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | MAIN BREAKERS         |
| Type                 | Sub feed main breaker |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 1.8 |

### Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | Generation - Renewable Energy - Alternative Energy<br>Other Generation - Conventional Energy - Conventional Energy<br>Datacenters - IT Space: CI and Hyper Converged<br>Marine Vessels and Equipment - Marine Vessels and Equipment - Other |
| standard    | UL 489, Federal Specifications Classification W-C375  |