



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR230ST Type BR BRKR 30A/2 Pole 120/240V 10K W/Shunt Trip *Eaton Corp*

Catalog Number	BR230ST
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR Breakers, 30 A, 10 Kaic, Two-Pole, 120/240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters, Shunt Trip Included
Weight per unit	1.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

dimensions	4.5000 IN X 4.2500 IN X 4.0000 IN
interrupt rating	10 kAIC
Poles	2
Trip Type	Common breaker trip
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 30A/2 POLE 120/240V 10K W/SHUNT TRIP
extra long description	ETN BR230ST BR 30A/2 Pole 120/240V
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR breakers, 30 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters, Shunt trip included
Product Type	BR 30A/2 Pole 120/240V 10K W/Shunt Trip
Special Features	120Vac Shunt trip

Manufacturer Information

Brand	Eaton
GTIN	00786676000239
Manufacturers Part Number	BR230ST
UPC	786676000239

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

UL 489,Federal Specifications Classification W-C375