



Project:

Type:

Prepared By:

Date:



UPC: 019813750477

Features and Benefits

- Energy efficient replacement for incandescent and halogen reflector lamps
- Constructed from durable plastic which lowers risk of breakage
- Rated for use in enclosed and open fixtures in dry or damp locations
- Frosted lens produces smooth diffuse light
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- ENERGY STAR Compliant
- Dimmable with common dimmer types (see Dimmer Compatibility List)

Technical Specifications**Performance****Product Type:**

Reflector

Input Wattage:

13W

Lumens:

950lm

Efficacy:

73lm/W

L70 Lifespan:

25,000-Hour LED lifespan based on IESlm-70 results

Wattage Equivalency:

75W

LED Characteristics**Color Accuracy (CRI):**

80

Color Temperature:

3000K

Beam Angle:

110°

Electrical**Power Factor:**

>0.9

Dimmable:

Yes, down to 20%

Input Voltage:

120V

Operating Temperature:

-20°C to 40°C

Construction**Bulb Shape:**

BR40

Enclosure Material:

Plastic

Housing Finish:

White

Lens Finish:

Frosted

Installation**Base Type:**

E26 Edison

Other**Technology EQ:**

Incandescent

Compliance**UL Listed:**

Yes

Environment:

Damp / Enclosed

Rohs:

Mercury and UV free. RoHS-compliant components.

FCC:


Complies with Part 15B of the FCC Rules




Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	6	15.8	10.6	7
PALLET	360	47.2	37	34.8

Dimension



Light Distribution





Project:

Type:

Prepared By:

Date:



UPC: 019813750477

Features and Benefits

- Energy efficient replacement for incandescent and halogen reflector lamps
- Constructed from durable plastic which lowers risk of breakage
- Rated for use in enclosed and open fixtures in dry or damp locations
- Frosted lens produces smooth diffuse light
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- ENERGY STAR Compliant
- Dimmable with common dimmer types (see Dimmer Compatibility List)

Technical Specifications**Performance****Product Type:**

Reflector

Input Wattage:

13W

Lumens:

950lm

Efficacy:

73lm/W

L70 Lifespan:

25,000-Hour LED lifespan based on IESlm-70 results

Wattage Equivalency:

75W

LED Characteristics**Color Accuracy (CRI):**

80

Color Temperature:

3000K

Beam Angle:

110°

Electrical**Power Factor:**

>0.9

Dimmable:

Yes, down to 20%

Input Voltage:

120V

Operating Temperature:

-20°C to 40°C

Construction**Bulb Shape:**

BR40

Enclosure Material:

Plastic

Housing Finish:

White

Lens Finish:

Frosted

Installation**Base Type:**

E26 Edison

Other**Technology EQ:**

Incandescent

Compliance**UL Listed:**

Yes

Environment:

Damp / Enclosed

Rohs:

Mercury and UV free. RoHS-compliant components.

FCC:


Complies with Part 15B of the FCC Rules



Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	6	15.8	10.6	7
PALLET	360	47.2	37	34.8

Dimension



Light Distribution

