



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9
78620-0000, TX Dripping Springs
Phone: 737-317-5073
Fax: 737-317-5074

BR4080LQN200G 40/80C 200A QN Mlo Loadcenter

Eaton Corp

Catalog Number	BR4080LQN200G
Manufacturer	Eaton Corp
Description	Main Lug Load Center, 40 Spaces, 80 Circuits, 200 A, 120/240 V Ac, #1 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 34.13 In Overall Height
Weight per unit	33.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	59120
Box Size	M104D-731
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX86.6902centimetre
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	M104D-731
------	-----------

Descriptions

Description	40/80C 200A QN MLO LOADCENTER
extra long description	ETN BR4080LQN200G BR style 1-inch I

Manufacturer Information

GTIN	00786676026314
UPC	786676026314

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN LUG
unspsc code	MODULAR LINE CORD, TELEPHONE LINE EXTENSION CORD TYPE; 15 FT LENGTH IN FT; METALLIC COLOR FAMILY; SILVER MANUFACTURERS COLOR NAME; GC[T] BRAND; CONNECTOR TYPE MODULAR PLUG; CORD SIZE (6) 26 AWG



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9
78620-0000, TX Dripping Springs
Phone: 737-317-5073
Fax: 737-317-5074

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 33

Uses, Certifications, and Standards

Enclosure NEMA 1

Mounting Combination