

Specifications



Photo is representative



Eaton C0200E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 200 va

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0200E2AFB
UPC	786680420887
PRODUCT LENGTH/DEPTH	4.18 in
PRODUCT HEIGHT	5.29 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	8.9 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings

PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	200 VA
SECONDARY VOLTAGE	120/115/110 V

Miscellaneous

MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0200E2AFB
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton C0200E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 200 va

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0200E2AFB
UPC	786680420887
PRODUCT LENGTH/DEPTH	4.18 in
PRODUCT HEIGHT	5.29 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	8.9 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings

PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	200 VA
SECONDARY VOLTAGE	120/115/110 V

Miscellaneous

MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0200E2AFB
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

