

Specifications



Photo is representative



Eaton C0250E6U

Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°C, 250 va

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0250E6U
UPC	786680019135
PRODUCT LENGTH/DEPTH	5.866 in
PRODUCT HEIGHT	3.819 in
PRODUCT WIDTH	4.488 in
PRODUCT WEIGHT	14.7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cUL Certified UL Listed CSA Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

Physical Attributes

COIL MATERIAL Copper windings

DESIGN MTE

TAP SIZE None

Performance Ratings

PRIMARY VOLTAGE 208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V

TEMPERATURE RATING 55°C

VOLT AMPERE RATING 250 VA

SECONDARY VOLTAGE 99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - C0250E6U](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

