

# Specifications



## Eaton C0500E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 500 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0500E2AFB
<b>UPC</b>	786680420962
<b>PRODUCT LENGTH/DEPTH</b>	5.51 in
<b>PRODUCT HEIGHT</b>	6.14 in
<b>PRODUCT WIDTH</b>	5.23 in
<b>PRODUCT WEIGHT</b>	19.4 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
<b>PRODUCT TYPE</b>	Industrial control transformer



Powering Business Worldwide

## Physical Attributes

**COIL MATERIAL** Copper windings

**DESIGN** MTE

**TAP SIZE** None

## Miscellaneous

**MODIFICATION 1** Factory-mounted two-pole primary fuse block for non-rejection type fuses

**SPECIAL FEATURES** Primary fuse block

## Performance Ratings

**PRIMARY VOLTAGE** 220 x 440 V, 230 x 460 V, 240 x 480 V

**TEMPERATURE RATING** 55°C

**VOLT AMPERE RATING** 500 VA

**SECONDARY VOLTAGE** 120/115/110 V

## Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - C0500E2AFB](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.

# Specifications



## Eaton C0500E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 500 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0500E2AFB
<b>UPC</b>	786680420962
<b>PRODUCT LENGTH/DEPTH</b>	5.51 in
<b>PRODUCT HEIGHT</b>	6.14 in
<b>PRODUCT WIDTH</b>	5.23 in
<b>PRODUCT WEIGHT</b>	19.4 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
<b>PRODUCT TYPE</b>	Industrial control transformer



Powering Business Worldwide

## Physical Attributes

**COIL MATERIAL** Copper windings

**DESIGN** MTE

**TAP SIZE** None

## Miscellaneous

**MODIFICATION 1** Factory-mounted two-pole primary fuse block for non-rejection type fuses

**SPECIAL FEATURES** Primary fuse block

## Performance Ratings

**PRIMARY VOLTAGE** 220 x 440 V, 230 x 460 V, 240 x 480 V

**TEMPERATURE RATING** 55°C

**VOLT AMPERE RATING** 500 VA

**SECONDARY VOLTAGE** 120/115/110 V

## Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - C0500E2AFB](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.