

# Specifications

## Eaton C0500E6U



Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, cu magnet wire, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°C, 500 va

Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0500E6U
<b>UPC</b>	786680019159
<b>PRODUCT LENGTH/DEPTH</b>	7.008 in
<b>PRODUCT HEIGHT</b>	4.449 in
<b>PRODUCT WIDTH</b>	5.236 in
<b>PRODUCT WEIGHT</b>	25.6 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified cUL Certified UL Listed
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

## Performance Ratings

<b>PRIMARY VOLTAGE</b>	208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	500 VA
<b>SECONDARY VOLTAGE</b>	99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - C0500E6U</a>
--------------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications

## Eaton C0500E6U



Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, cu magnet wire, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°C, 500 va

Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0500E6U
<b>UPC</b>	786680019159
<b>PRODUCT LENGTH/DEPTH</b>	7.008 in
<b>PRODUCT HEIGHT</b>	4.449 in
<b>PRODUCT WIDTH</b>	5.236 in
<b>PRODUCT WEIGHT</b>	25.6 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified cUL Certified UL Listed
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

## Performance Ratings

PRIMARY VOLTAGE	208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	500 VA
SECONDARY VOLTAGE	99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0500E6U</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

