



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CCP1DCC Compact Circuit Protec 1P

Bussmann Fuses

Catalog Number	CCP1DCC
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series CCP UL98 Fusible Disconnect, UL98 Fusible Disconnect, Single-Pole, Class CC
Weight per unit	0.2200 (lbs/each)
Product Category	Small Dimension Fuses

Features

actuator	Padlockable Handle
amperage rating	30 Amp
connection	Box Lug/Spade
dimensions	3.6500 IN X 2.0700 IN X 3.1400 IN
indicator	Local Fuse Indication Light
Poles	Single-pole
Voltage Rating	80 Vdc

Dimensions and Weight

Size	2.10 In Width X 3.10 In Depth X 3.70 In Height
------	--

Descriptions

Description	COMPACT CIRCUIT PROTEC 1P
extra long description	EFSE CCP-1-DCC Compact Circuit Prot
Features	The revolutionary Bussmann™ series CCP with CUBEFuse™ is a fused branch circuit disconnect that requires up to 67% less space with ratings up to 600A. The CCP with CUBEFuse simplifies selective coordination and allows for isolation of individual branch circuit loads for safe work practices.
Long Description	Eaton Bussmann series CCP UL98 fusible disconnect, UL98 fusible disconnect, Single-pole, Class CC
Product Type	Compact Circuit Protec 1POLE Class CC DC
Special Features	Short Circuit Current Rating 20 kA, Fuse Type Class CC (DC Rated)

Manufacturer Information

Brand	Eaton
GTIN	00051712158114
Manufacturers Part Number	CCP-1-DCC
UPC	051712158114

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	UL98 fusible disconnect



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.22

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	35 MM DIN RAIL
Operating Temperature standard	-20 To 75 Deg C Contact Manufacturer, RoHS Compliant, Not Applicable