

# Specifications



Photo is representative



## Eaton C0300E2A

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 300 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0300E2A
<b>UPC</b>	786680422645
<b>PRODUCT LENGTH/DEPTH</b>	4.56 in
<b>PRODUCT HEIGHT</b>	4.22 in
<b>PRODUCT WIDTH</b>	4.5 in
<b>PRODUCT WEIGHT</b>	11 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Listed cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
<b>PRODUCT TYPE</b>	Industrial control transformer



Powering Business Worldwide

## Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

## Performance Ratings

<b>PRIMARY VOLTAGE</b>	220 x 440 V, 230 x 460 V, 240 x 480 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	300 VA
<b>SECONDARY VOLTAGE</b>	120/115/110 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0300E2A</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.

# Specifications



Photo is representative



## Eaton C0300E2A

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 300 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0300E2A
<b>UPC</b>	786680422645
<b>PRODUCT LENGTH/DEPTH</b>	4.56 in
<b>PRODUCT HEIGHT</b>	4.22 in
<b>PRODUCT WIDTH</b>	4.5 in
<b>PRODUCT WEIGHT</b>	11 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Listed cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
<b>PRODUCT TYPE</b>	Industrial control transformer



Powering Business Worldwide

## Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

## Performance Ratings

<b>PRIMARY VOLTAGE</b>	220 x 440 V, 230 x 460 V, 240 x 480 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	300 VA
<b>SECONDARY VOLTAGE</b>	120/115/110 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C0300E2A</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.