

Specifications

Eaton C0300E5E

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 300 va, cu magnet wire



Photo is representative



General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0300E5E
UPC	786680420429
PRODUCT LENGTH/DEPTH	5.118 in
PRODUCT HEIGHT	4.764 in
PRODUCT WIDTH	5.236 in
PRODUCT WEIGHT	15.5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified UL Listed cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings

PRIMARY VOLTAGE	200/220/440 V, 208/230/460 V, 240/480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	300 VA
SECONDARY VOLTAGE	23/110 V, 24/115 V, 25/120 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0300E5E
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

