

Specifications



Photo is representative



Eaton C0350E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 350 va

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Type MTE industrial control transformer |
| CATALOG NUMBER | C0350E2AFB |
| UPC | 786680420948 |
| PRODUCT LENGTH/DEPTH | 4.56 in |
| PRODUCT HEIGHT | 5.29 in |
| PRODUCT WIDTH | 4.5 in |
| PRODUCT WEIGHT | 11.6 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL Listed CSA Certified cUL Certified |
| CATALOG NOTES | Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability |

Physical Attributes

| | |
|---------------|-----------------|
| COIL MATERIAL | Copper windings |
| DESIGN | MTE |
| TAP SIZE | None |

Performance Ratings

| | |
|--------------------|---------------------------------------|
| PRIMARY VOLTAGE | 220 x 440 V, 230 x 460 V, 240 x 480 V |
| TEMPERATURE RATING | 55°C |
| VOLT AMPERE RATING | 350 VA |
| SECONDARY VOLTAGE | 120/115/110 V |

Miscellaneous

| | |
|------------------|--|
| MODIFICATION 1 | Factory-mounted two-pole primary fuse block for non-rejection type fuses |
| SPECIAL FEATURES | Primary fuse block |

Resources

| | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C0350E2AFB |
| WARRANTY GUIDES | Selling Policy 25-000 - Distribution and Control Products and Services |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton C0350E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 350 va

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Type MTE industrial control transformer |
| CATALOG NUMBER | C0350E2AFB |
| UPC | 786680420948 |
| PRODUCT LENGTH/DEPTH | 4.56 in |
| PRODUCT HEIGHT | 5.29 in |
| PRODUCT WIDTH | 4.5 in |
| PRODUCT WEIGHT | 11.6 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL Listed CSA Certified cUL Certified |
| CATALOG NOTES | Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability |



Powering Business Worldwide

Physical Attributes

| | |
|---------------|-----------------|
| COIL MATERIAL | Copper windings |
| DESIGN | MTE |
| TAP SIZE | None |

Performance Ratings

| | |
|--------------------|---------------------------------------|
| PRIMARY VOLTAGE | 220 x 440 V, 230 x 460 V, 240 x 480 V |
| TEMPERATURE RATING | 55°C |
| VOLT AMPERE RATING | 350 VA |
| SECONDARY VOLTAGE | 120/115/110 V |

Miscellaneous

| | |
|------------------|--|
| MODIFICATION 1 | Factory-mounted two-pole primary fuse block for non-rejection type fuses |
| SPECIAL FEATURES | Primary fuse block |

Resources

| | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - C0350E2AFB |
| WARRANTY GUIDES | Selling Policy 25-000 - Distribution and Control Products and Services |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

