

Specifications



Eaton CDR3023

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CDR receptacle |
| CATALOG NUMBER | CDR3023 |
| UPC | 662276276987 |
| PRODUCT LENGTH/DEPTH | 2.88 in |
| PRODUCT HEIGHT | 3.38 in |
| PRODUCT WIDTH | 3.38 in |
| PRODUCT WEIGHT | 2.2 lb |



Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

Product specifications

| | |
|------------------------|----------------------|
| AMPERAGE RATING | 30A |
| GROUNDING TYPE | Style 2 |
| CONFIGURATION | Two-wire, three-pole |
| VOLTAGE RATING | 600 Vac/250 Vdc |

Resources

| | |
|--------------------------------------|---|
| 3D CAD DRAWING PACKAGE | Eaton Crouse-Hinds CDR3023 3D drawing |
| BROCHURES | PowerMate Drilling Pin and Sleeve Devices brochure |
| CATALOGS | PowerMate Drilling Pin and Sleeve Devices catalog page |
| CERTIFICATION REPORTS | PowerMate Drilling Pin and Sleeve Devices UL certification (Receptacles) |
| INSTALLATION INSTRUCTIONS | IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - CDR3023 PowerMate Connectors |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

