## **Specifications**







## Eaton C0500E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°c, 500 va

General specifications	9
PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0500E2AFB
UPC	786680420962
PRODUCT LENGTH/DEPTH	5.51 in
PRODUCT HEIGHT	6.14 in
PRODUCT WIDTH	5.23 in
PRODUCT WEIGHT	19.4 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified cUL Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability



<b>Physical Attributes</b>	
COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

<b>Performance Ratings</b>	
PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	500 VA
SECONDARY VOLTAGE	120/115/110 V

Miscellaneous	
MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	C0500E2AFB

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc** 

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







