

# Eaton CCP15034CD RS

Catalog Number: CCP15034CD RS

Eaton Crouse-Hinds series PowerMate CCP plug, 150A, 0.875-1.906", Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CCP plug	CCP15034CD RS
	UPC
	662276277465
Product Length/Depth	Product Height
10.8 in	4.13 in
Product Width	Product Weight
4.13 in	2.2 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

150A

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

0.875-1.906"

### Voltage rating

600 Vac/250 Vdc

### Material

Copper-free aluminum

### Special features

Reverse service

## Resources

### Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

### Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

### Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

### Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

### Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CCP15034CD RS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CCP15034CD RS

Catalog Number: CCP15034CD RS

Eaton Crouse-Hinds series PowerMate CCP plug, 150A, 0.875-1.906", Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CCP plug	CCP15034CD RS
	UPC
	662276277465
Product Length/Depth	Product Height
10.8 in	4.13 in
Product Width	Product Weight
4.13 in	2.2 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

150A

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

0.875-1.906"

### Voltage rating

600 Vac/250 Vdc

### Material

Copper-free aluminum

### Special features

Reverse service

## Resources

### Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

### Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

### Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

### Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

### Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CCP15034CD RS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)