

# Specifications

## Eaton CCP3023BC



Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP3023BC
<b>UPC</b>	662276276536
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2.31 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	2.2 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

### Product specifications

<b>AMPERAGE RATING</b>	30A
<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Two-wire, three-pole
<b>CABLE DIAMETER</b>	0.390-1.375"

<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum

<b>Resources</b>	
<b>3D CAD DRAWING PACKAGE</b>	<a href="#">Eaton Crouse-Hinds CCP3023BC 3D drawing</a>
<b>BROCHURES</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices brochure</a>
<b>CATALOGS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)</a>
	<a href="#">PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing</a>
	<a href="#">IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CCP3023BC</a>
	<a href="#">PowerMate Connectors</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton CCP3023BC

Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP3023BC
<b>UPC</b>	662276276536
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2.31 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	2.2 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

### Product specifications

<b>AMPERAGE RATING</b>	30A
<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Two-wire, three-pole
<b>CABLE DIAMETER</b>	0.390-1.375"

<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum

<b>Resources</b>	
<b>3D CAD DRAWING PACKAGE</b>	<a href="#">Eaton Crouse-Hinds CCP3023BC 3D drawing</a>
<b>BROCHURES</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices brochure</a>
<b>CATALOGS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)</a>
	<a href="#">PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing</a>
	<a href="#">IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CCP3023BC</a>
	<a href="#">PowerMate Connectors</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

