



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CGB398SA 1 NPT Male Al Cord/Cab FTG Neo Bush *Crouse-Hinds*

Catalog Number	CGB398SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CGB Cable Gland, Cable Range Min/Max: 0.875-1.000", Non-Armoured and Tray Cable, Non-Armoured, Aluminum, General Purpose, 1" NPT, Form D
Weight per unit	N/A
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	3.2100 IN X 2.2500 IN X 2.2500 IN

Descriptions

Description	1 NPT MALE AL CORD/CAB FTG NEO BUSH
extra long description	CRS-H CGB398 SA 1 NPT MALE AL CORD/
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round
Long Description	Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.875-1.000", Non-armoured and tray cable, Non-armoured, Aluminum, General purpose, 1" NPT, Form D
Product Type	1 NPT Male Al Cord/Cab FTG Neo Bush
Special Features	Non-Armored Gland

Manufacturer Information

Brand	Eaton
GTIN	00782274100876
Manufacturers Part Number	CGB398 SA
UPC	782274100876

Taxonomies, Classifications, and Categories

Category Description	MISC FITTINGS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	Class I Div 2 UL (CANADA AND US)
Temperature Rating	-25 To 40 Deg C