



CGB499 1-1/4" Dia Male Cord Grip (1.000-1.188) *Crouse-Hinds*

Catalog Number	CGB499
Manufacturer	Crouse-Hinds
Description	Cord Gland, Steel With Zinc Electroplate and Chromate Finish Coat (Body, Gland Nut);Neoprene (Bushing) Material, CGB Model, 1 to 1.188 In Cable/Cord Size, 3.001 In Length, 2.25 In Diameter, Straight Male Connection, 1-1/4 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 1.1599 LB
Weight per unit	1.2 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	3.1400 IN X 2.2500 IN X 2.2500 IN

Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

Dimensions and Weight

Size	1-1/4 in
------	----------

Descriptions

Description	1-1/4" DIA MALE CORD GRIP (1.000-1.188)
extra long description	CRS-H CGB499 1 1/4 NPT MALE CORD/CA
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

Manufacturer Information

Brand	Eaton
GTIN	00782274135205
UPC	782274135205

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	1.1599

Uses, Certifications, and Standards

Enclosure standard	Class I Div 2
Temperature Rating	UL (CANADA AND US), CUL -25 To 40 Deg C