

Specifications



Eaton CH12L125R

Eaton CH main lug loadcenters,Cover included,Main lug only,125A,B,Copper,NEMA 3R,Metallic,Overhead,CH,12,12,Three-wire,Single-phase,120/240 V,#6-2/0 AWG

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH12L125R
UPC	782113097381
PRODUCT LENGTH/DEPTH	16.75 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.8 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

SPECIAL FEATURES	Cover included
TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Copper
FEED TYPE	Overhead
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	12
NUMBER OF SPACES	12
PHASE	Single-phase
VOLTAGE RATING	120/240 V
WIRE SIZE	#6-2/0 AWG
BOX SIZE	B
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH12L125R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

