



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CH24L125R 1PH/CH Loadcenter 125A Mlo 24 Cir. Cu Bus Nema 3R *Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | CH24L125R   |
| Manufacturer     | Eaton Corp  |
| Description      | Main Lug Load Center, 24 Spaces, 24 Circuits, 125 A, 120/240 V Ac, #6 to 2/0 Awg Wire Size, Metallic Material, Copper Bus Material, 14.31 In Overall Length, 5.19 In Overall Width, 21 In Overall Height, 38.9 LB |
| Weight per unit  | 38.9 (lbs/each)   |
| Product Category | Single Phase Main Lug Load Cen  |

### Features

|                  |     |
|------------------|-----|
| amperage rating  | 125 |
| max amps         | 125 |
| max spaces/poles | 24  |
| number of spaces | 24  |
| Phase            | 1   |

### Dimensions and Weight

|        |       |
|--------|-------|
| Depth  | 21    |
| Height | 5.19  |
| Size   | C     |
| Width  | 14.31 |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1PH/CH LOADCENTER 125A MLO 24 CIR. CU BUS NEMA 3R |
| extra long description | ETN CH24L125R Eaton CH main lug loa               |

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN  | 00782113097701      |
| UPC   | 782113097701        |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | LOADCENTERS & COVERS |
| Type                 | Main lug loadcenter  |

### Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 38.9 |

### Uses, Certifications, and Standards

|          |             |
|----------|-------------|
| standard | UL 50,UL 67 |
|----------|-------------|