



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode
79701-0000, TX Midland
Phone: 432-685-3108
Fax: 432-685-3706



CH18L3125C 3PH/CH Loadctr 125A Mlo 18 Cir. Cu Bus Nema 1

Eaton Corp

Catalog Number	CH18L3125C
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenter, Main Lug Only, 125 A, C, Copper, Nema 1, Metallic, Top/Bottom, CH, 18 Circuits, 18 Spaces, Four-Wire, Three-Phase, #1-4/0 Awg
Weight per unit	25.0 (lbs/each)
Product Category	Three Phase Main Lug Load Cent

Features

amperage rating	125
interrupt rating	35
number of spaces	18
Phase	3

Dimensions and Weight

Depth	21
Height	3.88
Size	C
Width	14.31

Descriptions

Description	3PH/CH LOADCNTR 125A MLO 18 CIR. CU BUS NEMA 1
extra long description	ETN CH18L3125C 3Ph/CH LC 125A MLO 1
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenter, Main lug only, 125 A, C, Copper, NEMA 1, Metallic, Top/bottom, CH, 18 Circuits, 18 Spaces, Four-wire, Three-phase, #1-4/0 AWG
Product Type	3PH/CH LC 125A Mlo 18 CKT Cu Bus Nema 1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113097534
Manufacturers Part Number	CH18L3125C
UPC	782113097534



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode
79701-0000, TX Midland
Phone: 432-685-3108
Fax: 432-685-3706

Taxonomies, Classifications, and Categories

Category Description LOADCENTERS & COVERS

Type Main lug loadcenter

Packaging

Carton 1

Weight Per each 25

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard UL 50,UL 67