



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CH280 Type CH BRKR 80A/2 Pole 120/240V 10K

*Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | CH280   |
| Manufacturer     | Eaton Corp  |
| Description      | Standard Trip Circuit Breaker, 80 A, Common Tripping Mechanism, Plug-On, 120/240 V Ac, 0.75 In Overall Width, 0.57 LB |
| Weight per unit  | 0.5700 (lbs/each)   |
| Product Category | 2 Pole Standard Trip Plug-In  |

### Features

|            |                                   |
|------------|-----------------------------------|
| dimensions | 3.5000 IN X 1.5000 IN X 3.5000 IN |
| Poles      | Two-pole                          |
| Trip Type  | Common breaker trip               |

### Descriptions

|                        |                                      |
|------------------------|--------------------------------------|
| Description            | TYPE CH BRKR 80A/2 POLE 120/240V 10K |
| extra long description | ETN CH280 Type CH Breaker 80A/2 Pol  |

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN  | 00782113312293      |
| UPC   | 782113312293        |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Loadcenter Plug In Breakers and Accessories |
| Type                 | Thermal magnetic circuit breakers           |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 5    |
| Weight Per each | 0.57 |

### Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Marine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyOtherDatacenters - IT Space: CI and Hyper Converged |
| standard    | UL 489   |