

# Specifications



Photo is representative



## Eaton CH8NLJS

Eaton CH Indoor Surface Cover, Surface cover, J, NEMA 1, CH, Surface, 0.75 in, CH32nlpn225j

### General specifications

<b>PRODUCT NAME</b>	Eaton CH cover
<b>CATALOG NUMBER</b>	CH8NLJS
<b>UPC</b>	782116110384
<b>PRODUCT LENGTH/DEPTH</b>	34.1 in
<b>PRODUCT HEIGHT</b>	1.1 in
<b>PRODUCT WIDTH</b>	14.3 in
<b>PRODUCT WEIGHT</b>	8.6 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	Contact Manufacturer
<b>CATALOG NOTES</b>	Designed for main lug only/convertible plug-on neutral loadcenters



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Cover
<b>AMPERAGE RATING</b>	400 A
<b>BUS MATERIAL</b>	Aluminum
<b>MOUNTING</b>	Surface
<b>PHASE</b>	Three-phase
<b>USED WITH</b>	Ch32nlpn225j
<b>BOX SIZE</b>	J
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	10 kAIC

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
MULTIMEDIA	<a href="#">AFCI Educational Video</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CH8NLJS</a>
WARRANTY GUIDES	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.