



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHCC3DU 3POLE 30A 600V MFH For 10X38 Class CC

Bussmann Fuses

Catalog Number	CHCC3DU
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series CHCC Modular Fuse Holder, 600 VDC, 30 A, Three-Pole
Weight per unit	0.2200 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	30
class	Class CC
dimensions	2.7165 IN X 3.2677 IN X 2.9134 IN
media	Yes
Voltage Rating	600 Vdc

Dimensions and Weight

Size	2.067 In Width X 3.275 In Depth X 2.909 In Height
------	---

Descriptions

Description	3POLE 30A 600V MFH FOR 10X38 CLASS CC
extra long description	BUSS CHCC3DU CCP
Features	Bussmann series Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applicat
Long Description	Eaton Bussmann series CHCC modular fuse holder, 600 Vdc, 30 A, Three-pole
Product Type	CCP
Special Features	3 Pole, For Use With KTK-R, LP-CC and FNQ-R Class CC fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712362696
Manufacturers Part Number	CHCC3DU
UPC	051712362696

Taxonomies, Classifications, and Categories

Category Description	FUSE BLOCKS,FUSE HOLDERS
Type	Modular fuse holder



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	0.22

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Operating Temperature standard	-20 To 120 Deg C Contact Manufacturer, RoHS Compliant