

Eaton CHP18B100X2

Catalog Number: CHP18B100X2

Eaton CH main breaker loadcenters,PON,Main breaker,100 A,X2,Copper,X2,NEMA 1,Metallic,10 kAIC,CH,36,18,Three-wire,Single-phase,#6-1/0 AWG,120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP18B100X2
UPC	Product Length/Depth
786679189481	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
12.2 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Purchase Size X2 Cover Separately

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Cover

X2

Main circuit breaker

CH

Number of circuits

36

Number of spaces

18

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP18B100X2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)