



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHP42N225R CH Pon Loadcntr 225A Convertible 42 Space N3R *Eaton Corp*

Catalog Number	CHP42N225R
Manufacturer	Eaton Corp
Description	Eaton CH Plug-On Neutral Loadcenter, 225A, Convertible, 42 Spaces, Nema 3R
Weight per unit	33.0 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

amperage rating	225
dimensions	37.0000 IN X 14.3100 IN X 5.1900 IN
interrupt rating	10
media	Yes
number of spaces	42
Phase	1

### Dimensions and Weight

Depth	37.0000
Height	5.1900
Size	X7
Width	14.3100

### Descriptions

Description	CH PON LOADCNTR 225A CONVERTIBLE 42 SPACE N3R
extra long description	ETN CHP42N225R CH PON LC, 225A, CON
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH plug-on neutral loadcenter, 225A, convertible, 42 spaces, NEMA 3R
Product Type	CH Pon LC, 225A, Conv, 42SP, N3R
Special Features	Cover included

### Manufacturer Information

Brand	Eaton
GTIN	00786689058746
Manufacturers Part Number	CHP42N225R
UPC	786689058746



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description.....LOADCENTERS & COVERS

Type.....Convertible loadcenter

## Packaging

Carton.....1

Weight Per each.....33

## Uses, Certifications, and Standards

Application.....Residential Bldgs & Facilities - Residential Bldgs & Facilities -

.....Other

standard.....UL 50,UL 67