

Specifications



Eaton CHU1N7N4NS

Eaton pedestal mount unmetered, Unmetered, 50A, 20A, 30A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 14-50R, NEMA 5-20R2GFI, NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V

General specifications

PRODUCT NAME	Eaton pedestal mount unmetered
CATALOG NUMBER	CHU1N7N4NS
UPC	782114203828
PRODUCT LENGTH/DEPTH	4.3 in
PRODUCT HEIGHT	17.1 in
PRODUCT WIDTH	9.5 in
PRODUCT WEIGHT	16 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588



Powering Business Worldwide

Product specifications

TYPE	Unmetered
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER	Non-ground fault

Resources

CATALOGS	Residential and Light Commercial Power Pedestals, Volume 1 Tab 5
-----------------	--

POSITION 2	
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA TT-30R
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHU1N7N4NS
--------------------------------------	--

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
 All other trademarks are property of their respective owners.



Specifications



Eaton CHU1N7N4NS

Eaton pedestal mount unmetered, Unmetered, 50A, 20A, 30A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 14-50R, NEMA 5-20R2GFI, NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V

General specifications

PRODUCT NAME	Eaton pedestal mount unmetered
CATALOG NUMBER	CHU1N7N4NS
UPC	782114203828
PRODUCT LENGTH/DEPTH	4.3 in
PRODUCT HEIGHT	17.1 in
PRODUCT WIDTH	9.5 in
PRODUCT WEIGHT	16 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588



Powering Business Worldwide

Product specifications

TYPE	Unmetered
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER	Non-ground fault

Resources

CATALOGS	Residential and Light Commercial Power Pedestals, Volume 1 Tab 5
-----------------	--

POSITION 2	
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA TT-30R
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHU1N7N4NS
--------------------------------------	--

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
 All other trademarks are property of their respective owners.

