

Specifications



Eaton CHR7N7NS

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Top, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 5-20R2GFI, Right: None, Ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR7N7NS
UPC	782114203293
PRODUCT LENGTH/DEPTH	31 in
PRODUCT HEIGHT	8 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	24 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231



Powering Business Worldwide

Product specifications

TYPE	Metered-ringless
UTILITY APPROVALS	IA : Alliant (IP&L and WP&L) WI : Alliant (IP&L and WP&L) FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) FL : Tallahassee City Electric
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	None
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 5-20R2GFI
RECEPTACLE RIGHT	None
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources

CATALOGS

[Residential and Light Commercial Power Pedestals, Volume 1 Tab 5](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHR7N7NS](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton CHR7N7NS

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Top, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 5-20R2GFI, Right: None, Ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR7N7NS
UPC	782114203293
PRODUCT LENGTH/DEPTH	31 in
PRODUCT HEIGHT	8 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	24 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231



Powering Business Worldwide

Product specifications

TYPE	Metered-ringless
UTILITY APPROVALS	IA : Alliant (IP&L and WP&L) WI : Alliant (IP&L and WP&L) FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) FL : Tallahassee City Electric
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	None
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 5-20R2GFI
RECEPTACLE RIGHT	None
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources

CATALOGS

[Residential and Light Commercial Power Pedestals, Volume 1 Tab 5](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHR7N7NS](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

