

# SAFETY DATA SHEET

## 1. Identification

Product identifier	Kopr-Shield		
Other means of identification			
SDS number	SDS-00003		
Product code	201-31879, 201-31879-1, CP128, CP16, CP8-TB, 54865CK		
Recommended use	Lubricants, Greases and Release Products		
Recommended restrictions	None known.		
Manufacturer/Importer/Supplier/	Distributor information		
Company name Address Telephone	Thomas & Betts Corporation 8155 T & B Boulevard Memphis, TN 38125 US 901-252-5000 ext.8324		
E-mail Emergency phone number	Not available. For Hazardous Materials [or Dangerous Goods] Incident Spill, Leak, Fire, Exposure, or Accident Call CHEMTREC Day or Night +1 703-741-5970		
2. Hazard(s) identification			
Physical hazards	Not classified.		
Health hazards	Not classified.		
OSHA defined hazards	Not classified.		
Label elements			

Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	The mixture does not meet the criteria for classification.
Precautionary statement	
Prevention	Observe good industrial hygiene practices.
Response	Wash hands after handling.
Storage	Store away from incompatible materials.
Disposal	Dispose of waste and residues in accordance with local authority requirements.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	Very toxic to aquatic life. Harmful to aquatic life with long lasting effects.

## 3. Composition/information on ingredients

### **Mixtures**

Chemical name	CAS number	%
Lubricating greases; a complex combination of hydrocarbons having carbon numbers predominantly in the range of C12 through C50. May contain organic salts of alkali metals, alkaline earth metals, etc.	74869-21-9	65 - 70
Copper	7440-50-8	25-30
Zinc bis(dipentyldithiocarbamate)	15337-18-5	<1

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures	
Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.
5. Fire-fighting measures	
Suitable extinguishing media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	None known.
Special protective equipment and precautions for firefighters	Firefighters should wear full protective clothing including self contained breathing apparatus. Wear suitable protective equipment.
Fire fighting equipment/instructions	Use standard firefighting procedures and consider the hazards of other involved materials.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.
6. Accidental release meas	sures
Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. For personal protection, see section 8 of the SDS. Wear suitable protective clothing, gloves and eye/face protection.
Methods and materials for containment and cleaning up	Stop leak if you can do so without risk. Prevent entry into waterways, sewers, basements or confined areas. The product is immiscible with water and will spread on the water surface. Should not be released into the environment. Be aware of potential for surfaces to become slippery.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Environmental precautionsNever return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.Prevent further leakage or spillage if safe to do so. Do not contaminate water.

## 7. Handling and storage

**Precautions for safe handling** Wear personal protective equipment. Avoid contact with skin, eyes and clothing. Remove contaminated clothing and wash before reuse. Do not breathe vapors or spray mist. In case of insufficient ventilation, wear suitable respiratory equipment. Use only in area provided with appropriate exhaust ventilation. Be aware of potential for surfaces to become slippery. Do not eat, drink or smoke when using the product.

**Conditions for safe storage, including any incompatibilities** Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of children. Store away from incompatible materials (see Section 10 of the SDS).

## 8. Exposure controls/personal protection

### **Occupational exposure limits**

## US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Туре	Value	Form
Copper (CAS 7440-50-8)	PEL	1 mg/m3	Dust and mist.
		0.1 mg/m3	Fume.
US. ACGIH Threshold Limi	it Values		
Components	Туре	Value	Form
Copper (CAS 7440-50-8)	TWA	1 mg/m3	Dust and mist.
		0.2 mg/m3	Fume.
US. NIOSH: Pocket Guide	to Chemical Hazards		
Components	Туре	Value	Form
Copper (CAS 7440-50-8)	TWA	1 mg/m3	Dust and mist.
ological limit values	No biological exposure limits noted for	or the ingredient(s).	
kposure guidelines	No exposure standards allocated. Occupational Exposure Limits are not relevant to the current physical form of the product.		
ppropriate engineering ontrols	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.		
dividual protection measures	s, such as personal protective equipm	ent	
Eye/face protection	Wear safety glasses with side shield	s (or goggles).	
Skin protection			
Hand protection	Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.		
Skin protection			
Other	Wear apron or protective clothing in case of contact. Use of protective coveralls and long sleeves is recommended.		
<b>Respiratory protection</b>	In case of insufficient ventilation, wear suitable respiratory equipment.		
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.		
eneral hygiene onsiderations	When using, do not eat, drink or smo as washing after handling the materia		

## 9. Physical and chemical properties

Appearance			
Physical state	Semi-fluid (gel).		
Form	Gel.		
Color	Copper.		
Odor	Petroleum.		
Odor threshold	Not available.		
рН	Neutral		
Melting point/freezing point	NONE.		
Initial boiling point and boiling range	> 599 °F (> 315 °C)		
Flash point	> 590.0 °F (> 310.0 °C)		
Evaporation rate	Not available.		
Flammability (solid, gas)	Not applicable.		
Upper/lower flammability or explosive limits			
Flammability limit - lower (%)	Not applicable.		

Flammability limit - upper (%)	Not applicable.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	1.2
Solubility(ies)	
Solubility (water)	Insoluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not applicable.
Other information	
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.

## 10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions. Decomposes in the presence of water.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Acids. Oxidizing agents. Acetylene. Vinyl compounds.
Hazardous decomposition products	Metal oxides.

## 11. Toxicological information

## Information on likely routes of exposure

Inhalation	No adverse effects due to inhalation are expected.			
Skin contact	No adverse effects due to skin contact are expected.			
Eye contact	Direct contact with eyes may cause temporary irritation.			
Ingestion	Expected to be a low ingestion hazard.			
Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.			

### Information on toxicological effects

Acute toxicity	Not expected to be acutely toxic.		
Product	Species	Test Results	
Kopr-Shield (CAS Mixture)			
Acute			
Oral			
LD50		3266 mg/kg, Acute toxicity estimate	
* Estimates for product m	nay be based on additional component dat	a not shown.	
Skin corrosion/irritation	No adverse effects due to skin cont	tact are expected.	
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.		
Respiratory or skin sensitiz	ation		
Respiratory sensitization	n Not a respiratory sensitizer.		
Skin sensitization	This product is not expected to cau	se skin sensitization.	

Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
IARC Monographs. Overall I	Evaluation of Carcinogenicity
Not listed.	
NTP Report on Carcinogens	6
Not listed.	
OSHA Specifically Regulate	d Substances (29 CFR 1910.1001-1050)
Not regulated.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not an aspiration hazard.
Further information	This product has no known adverse effect on human health.

## **12. Ecological information**

Ecotoxicity	Very toxic to aquatic life.	. Harmful to aquatic life with	n long lasting effects.

Components		Species	Test Results
Copper (CAS 7440-50-8)			
Aquatic			
Algae	EC50	Pseudokirchnerella subcapitata	0.031 - 0.054 mg/l, 96 hours
Crustacea	EC50	Water flea (Daphnia magna)	0.03 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	0.0068 - 0.0156 mg/l, 96 hours

\* Estimates for product may be based on additional component data not shown.

Persistence and degradability	No data is available on the degradability of this product.
Bioaccumulative potential	The product is not expected to bioaccumulate.
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

## 13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Dispose of contents/container in accordance with local/regional/national/international regulations.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers retain product residue, follow label warnings even after container is emptied.

## 14. Transport information

DOT	
UN number	UN3082
UN proper shipping name	Environmentally hazardous substances, liquid, n.o.s. (Copper RQ = 18182 LBS)
Transport hazard class(es)	
Class	9
Subsidiary risk	-
Label(s)	9
Packing group	III

Environmental hazards Marine pollutant Special precautions for user Special provisions Packaging exceptions Packaging non bulk Packaging bulk	Yes. Read safety instructions, SDS and emergency procedures before handling. 8, 146, 335, IB3, T4, TP1, TP29 155 203 241
UN number	UN3082
UN proper shipping name	Environmentally hazardous substance, liquid, n.o.s. (Copper)
Transport hazard class(es)	
Class	9
Subsidiary risk	•
Packing group	III
Environmental hazards	Yes.
ERG Code	9L
· ·	Read safety instructions, SDS and emergency procedures before handling.
IMDG	
UN number	UN3082
UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (COPPER)
Transport hazard class(es)	
Class	9
Subsidiary risk	
Packing group	III
Environmental hazards	
Marine pollutant	YES.
EmS	F-A, S-F
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable.
15. Regulatory information	
US federal regulations	This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

Not regulated.

### CERCLA Hazardous Substance List (40 CFR 302.4)

Copper (CAS 7440-50-8)	LISTED
Zinc bis(dipentyldithiocarbamate) (CAS 15337-18-5)	LISTED

### Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories	Immediate Hazard - No Delayed Hazard - No Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No
SARA 302 Extremely hazard	ous substance
Not listed.	
SARA 311/312 Hazardous chemical	No

### SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.	
Copper	7440-50-8	25-30	
Zinc bis(dipentyldithiocarbamate)	15337-18-5	<1	

### Other federal regulations

#### Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

### Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act Not regulated. (SDWA)

### **US** state regulations

**US. Massachusetts RTK - Substance List** 

Copper (CAS 7440-50-8)

### US. New Jersey Worker and Community Right-to-Know Act

Copper (CAS 7440-50-8)

Zinc bis(dipentyldithiocarbamate) (CAS 15337-18-5)

### US. Pennsylvania Worker and Community Right-to-Know Law

Copper (CAS 7440-50-8)

### US. Rhode Island RTK

Copper (CAS 7440-50-8) Zinc bis(dipentyldithiocarbamate) (CAS 15337-18-5)

### **US. California Proposition 65**

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

### International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

\*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

## 16. Other information, including date of preparation or last revision

Issue date	15-January-2016
Revision date	04-May-2016
Revision #	2
Further information	HMIS Hazard Scale: 0 = Minimal 1 = Slight 2 = Moderate 3 = Serious 4 = Severe * = Chronic hazard NFPA Hazard Scale: 0 = Minimal 1 = Slight 2 = Moderate 3 = Serious 4 = Severe
HMIS® ratings	Health: 0 Flammability: 1 Physical hazard: 0
NFPA ratings	

List of abbreviations	DOT: Department of Transportation. IATA: International Air Transport Association. IMDG: International Maritime Dangerous Goods. HMIS: Hazardous Materials Identification System. NFPA: National Fire Protection Association. CAS Number: Chemical Abstracts Service Registry Number. LC50: Lethal concentration 50% (concentration that kills 50% of test animals). EC50: (Effective Concentration – 50%) The concentration that will produce a 50% in vivo inhibition of a biological or biochemical effect, in the test organisms or animals. MARPOL: International Convention for the Prevention of Pollution from Ships.
Disclaimer	The information presented herein has been compiled from resources considered to be dependable and accurate to the best of Thomas & Betts Corporation knowledge. The information relates to the special material. It may not be valid for this material if used in combination with any other materials or in any other process. It is user's responsibility to satisfy himself as to the suitability and completeness of this information for his own particular use. Thomas & Betts Corporation cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.