



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106



CS420I 20A 120/277VAC B+S Wire Comm 4W SW Iv

Pass & Seymour/Legrand

Catalog Number	CS420I
Manufacturer	Pass & Seymour/Legrand
Description	Construction 4-Way Switch, Back and Side-Wire, 20A 120/277V.
Weight per unit	0.1700 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Four pole
actuator	Toggle
amperage rating	20
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, Halogen, LED, Xenon, CFL, Universal, Fluorescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE COMM 4W SW IV
extra long description	P&S CSB20AC4I 20A 120/277VAC B+S WI
Features	Single Piece Plated Steel Mounting Strap
Long Description	Construction 4-Way Switch, Back and Side-Wire, 20A 120/277V.
Product Type	20A 120/277VAC B+S Wire Comm 4W SW I
Special Features	Back & side wire, locking support, heavy duty toggle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126372
Manufacturers Part Number	CSB20AC4I
UPC	785007126372

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.17

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting standard	WALL UL, CSA, FEDSPEC, CULUS, UL 498/20, FEDSPEC