



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG134061FNC21C DG1 480V FR4 N1 40HP 61A CT 50HP 72A VT

Eaton Corp

Catalog Number	DG134061FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 61A 400V Input Three-Phase Mains Connection/Three-Phase Motor Connection Internal Emc Filter Graphic LCD Display and Keypad , Nema 1
Weight per unit	77.5 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	400 V

Dimensions and Weight

Depth	15
Height	18.5
Width	28

Descriptions

Description	DG1 480V FR4 N1 40HP 61A CT 50HP 72A VT
extra long description	ETN DG1-34061FN-C21C DG1,480V FR4 ,
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 61A 400V input Three-phase mains connection/three-phase motor connection Internal EMC filter Graphic LCD display and keypad , NEMA 1
Product Type	DG1, 480V FR4 , N1, 40HP, 61A CT, 50HP, 72A VT

Manufacturer Information

Brand	Eaton
GTIN	00786685878812
Manufacturers Part Number	DG1-34061FN-C21C
UPC	786685878812

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	77.5

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL cULCE IEC/EN 61800-5-1 IEC 61800-5-2 UL 508C IEC 61508 EN 62061 EN ISO 13849-1,CE Marked,RoHS Compliant,C-Tick Compliant