



## Material Safety Data Sheet

Copyright, 2014, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

**PRODUCT NAME:** 3M™ Direct Bury Splice Kits, DBR/Y-6 & DBO/B-6  
**MANUFACTURER:** 3M  
**DIVISION:** Electrical Markets Division  
**ADDRESS:** 3M Center, St. Paul, MN 55144-1000, USA  
**Telephone:** 1-888-3M HELPS (1-888-364-3577)

**EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)**

**Issue Date:** 09/09/14  
**Supersedes Date:** Initial Issue  
**Document Group:** 33-9322-0

### ID Number(s):

80-6114-3724-7, 80-6114-3725-4, 80-6114-5718-7, 80-6114-5719-5, 80-6114-6728-5, 80-6114-6729-3

**This product is a kit or a multipart product which consists of multiple, independently packaged components. An SDS for each of these components is included. Please do not separate the component SDSs from this cover page. The document numbers of the SDSs for components of this product are:**

26-7488-5

No revision information is available.

**DISCLAIMER:** The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

**3M USA SDSs are available at [www.3M.com](http://www.3M.com)**





## Safety Data Sheet

Copyright,2017,3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document Group:</b>	26-7488-5	<b>Version Number:</b>	2.02
<b>Issue Date:</b>	01/27/17	<b>Supersedes Date:</b>	09/11/15

### SECTION 1: Identification

#### 1.1. Product identifier

3M™Direct Bury Splice with Sealant

#### 1.2. Recommended use and restrictions on use

##### Recommended use

Electrical, Moisture sealing connectors for low voltage connection.

#### 1.3. Supplier's details

<b>MANUFACTURER:</b>	3M
<b>DIVISION:</b>	Electrical Markets Division
<b>ADDRESS:</b>	3M Center, St. Paul, MN 55144-1000, USA
<b>Telephone:</b>	1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

### SECTION 2: Hazard identification

#### 2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

#### 2.2. Label elements

##### Signal word

Not applicable.

##### Symbols

Not applicable.

##### Pictograms

Not applicable.

#### 2.3. Hazards not otherwise classified

None.

6% of the mixture consists of ingredients of unknown acute oral toxicity.

**SECTION 3: Composition/information on ingredients**

Ingredient	C.A.S. No.	% by Wt
WHITE MINERAL OIL GREASE	8042-47-5	40 - 60
Ethylene/propylene copolymer tube	9010-79-1	30 - 50
Arylalkylene Copolymer	Trade Secret*	2 - 6

\*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

**SECTION 4: First aid measures****4.1. Description of first aid measures****Inhalation:**

No need for first aid is anticipated.

**Skin Contact:**

Wash with soap and water. If signs/symptoms develop, get medical attention.

**Eye Contact:**

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

**If Swallowed:**

Rinse mouth. If you feel unwell, get medical attention.

**4.2. Most important symptoms and effects, both acute and delayed**

See Section 11.1. Information on toxicological effects.

**4.3. Indication of any immediate medical attention and special treatment required**

Not applicable.

**SECTION 5: Fire-fighting measures****5.1. Suitable extinguishing media**

In case of fire: Use a carbon dioxide or dry chemical extinguisher to extinguish.

**5.2. Special hazards arising from the substance or mixture**

None inherent in this product.

**Hazardous Decomposition or By-Products****Substance**

Hydrocarbons  
Carbon monoxide  
Carbon dioxide

**Condition**

During Combustion  
During Combustion  
During Combustion

**5.3. Special protective actions for fire-fighters**

No special protective actions for fire-fighters are anticipated.

**SECTION 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Observe precautions from other sections.

**6.2. Environmental precautions**

Avoid release to the environment.

**6.3. Methods and material for containment and cleaning up**

Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue. Seal the container. Dispose of collected material as soon as possible.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

For industrial or professional use only. Do not eat, drink or smoke when using this product. Wash thoroughly after handling.

**7.2. Conditions for safe storage including any incompatibilities**

No special storage requirements.

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational exposure limits**

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
MINERAL OILS, HIGHLY-REFINED OILS	8042-47-5	ACGIH	TWA(inhalable fraction):5 mg/m <sup>3</sup>	A4: Not class. as human carcin
Paraffin oil	8042-47-5	OSHA	TWA(as mist):5 mg/m <sup>3</sup>	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

**8.2. Exposure controls****8.2.1. Engineering controls**

No engineering controls required.

**8.2.2. Personal protective equipment (PPE)****Eye/face protection**

None required.

**Skin/hand protection**

No chemical protective gloves are required.

**Respiratory protection**

None required.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

General Physical Form:	Solid Connector
Specific Physical Form:	Viscous Sealant
Odor, Color, Grade:	various colors
Odor threshold	<i>No Data Available</i>
pH	<i>No Data Available</i>
Melting point	<i>No Data Available</i>
Boiling Point	<i>Not Applicable</i>
Flash Point	No flash point
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Vapor Pressure	<i>Not Applicable</i>
Vapor Density	<i>Not Applicable</i>
Density	<i>Not Applicable</i>
Specific Gravity	0.95 [Details: (Sealant)]
Solubility in Water	Nil
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>Not Applicable</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	<i>No Data Available</i>
Average particle size	<i>No Data Available</i>
Bulk density	<i>No Data Available</i>
Hazardous Air Pollutants	<i>No Data Available</i>
Molecular weight	<i>No Data Available</i>
Volatile Organic Compounds	<i>No Data Available</i>
Percent volatile	<i>No Data Available</i>
Softening point	<i>No Data Available</i>
VOC Less H2O & Exempt Solvents	<i>No Data Available</i>

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

### 10.2. Chemical stability

Stable.

### 10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

### 10.4. Conditions to avoid

None known.

### 10.5. Incompatible materials

None known.

### 10.6. Hazardous decomposition products

**Substance**

None known.

**Condition**

Refer to section 5.2 for hazardous decomposition products during combustion.

## SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

### 11.1. Information on Toxicological effects

#### Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

#### Inhalation:

No known health effects.

#### Skin Contact:

Contact with the skin during product use is not expected to result in significant irritation.

#### Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

#### Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

#### Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

#### Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
WHITE MINERAL OIL GREASE	Dermal	Rabbit	LD50 > 2,000 mg/kg
WHITE MINERAL OIL GREASE	Ingestion	Rat	LD50 > 5,000 mg/kg
Ethylene/propylene copolymer tube	Dermal	Rabbit	LD50 > 2,000 mg/kg
Ethylene/propylene copolymer tube	Ingestion	Rat	LD50 > 5,000 mg/kg

ATE = acute toxicity estimate

#### Skin Corrosion/Irritation

Name	Species	Value
WHITE MINERAL OIL GREASE	Rabbit	No significant irritation
Ethylene/propylene copolymer tube	Rabbit	No significant irritation

#### Serious Eye Damage/Irritation

Name	Species	Value
WHITE MINERAL OIL GREASE	Rabbit	Mild irritant
Ethylene/propylene copolymer tube	Rabbit	No significant irritation

**Skin Sensitization**

Name	Species	Value
WHITE MINERAL OIL GREASE	Guinea pig	Not sensitizing

**Respiratory Sensitization**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Germ Cell Mutagenicity**

Name	Route	Value
WHITE MINERAL OIL GREASE	In Vitro	Not mutagenic

**Carcinogenicity**

Name	Route	Species	Value
WHITE MINERAL OIL GREASE	Dermal	Mouse	Not carcinogenic
WHITE MINERAL OIL GREASE	Inhalation	Multiple animal species	Not carcinogenic

**Reproductive Toxicity****Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test Result	Exposure Duration
WHITE MINERAL OIL GREASE	Ingestion	Not toxic to female reproduction	Rat	NOAEL 4,350 mg/kg/day	13 weeks
WHITE MINERAL OIL GREASE	Ingestion	Not toxic to male reproduction	Rat	NOAEL 4,350 mg/kg/day	13 weeks
WHITE MINERAL OIL GREASE	Ingestion	Not toxic to development	Rat	NOAEL 4,350 mg/kg/day	during gestation

**Target Organ(s)****Specific Target Organ Toxicity - single exposure**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Specific Target Organ Toxicity - repeated exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
WHITE MINERAL OIL GREASE	Ingestion	hematopoietic system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1,381 mg/kg/day	90 days
WHITE MINERAL OIL GREASE	Ingestion	liver   immune system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1,336 mg/kg/day	90 days

**Aspiration Hazard**

Name	Value
WHITE MINERAL OIL GREASE	Aspiration hazard

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

**SECTION 12: Ecological information****Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material



and/or its components.

### Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

## SECTION 13: Disposal considerations

### 13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. If no other disposal options are available, waste product may be placed in a landfill properly designed for industrial waste.

**EPA Hazardous Waste Number (RCRA):** Not regulated

## SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: Regulatory information

### 15.1. US Federal Regulations

Contact 3M for more information.

### 311/312 Hazard Categories:

Fire Hazard - No      Pressure Hazard - No      Reactivity Hazard - No      Immediate Hazard - No      Delayed Hazard - No

### 15.2. State Regulations

Contact 3M for more information.

### 15.3. Chemical Inventories

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

### 15.4. International Regulations

Contact 3M for more information.

**This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.**

## SECTION 16: Other information

### NFPA Hazard Classification

**Health:** 0 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include

the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

<b>Document Group:</b>	26-7488-5	<b>Version Number:</b>	2.02
<b>Issue Date:</b>	01/27/17	<b>Supersedes Date:</b>	09/11/15

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

**3M USA SDSs are available at [www.3M.com](http://www.3M.com)**