



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5617 Andrews Hwy
79762-0000, TX Odessa
Phone: 432-366-0008
Fax: 432-366-6045



DH325NRK 400A/3P HD Fusible Safety Switch W/Neut 240V Nema

Eaton Corp

Catalog Number	DH325NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 400 A, Nema 3R, Painted Galvanized Steel, Class H, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 50, 125/ 50 HP (3PH @STD, TD/250 VDC), (2)#1/0-(2)300 Kcmil or (1)#1/0-(1)750 Kcmil Al
Weight per unit	120.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	400
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	7.27
Height	44.74
Width	23.08

Descriptions

Description	400A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH325NRK 400A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 400 A, NEMA 3R, Painted galvanized steel, Class H, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 50, 125/ 50 hp (3PH @Std, TD/250 Vdc), (2)#1/0-(2)300 kcmil or (1)#1/0-(1)750 kcmil Al
Product Type	400A/3P HD FSBL Sfty SW W/Neut 240V N3R

Manufacturer Information

Brand	Eaton
GTIN	00782113207070
Manufacturers Part Number	DH325NRK
UPC	782113207070

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5617 Andrews Hwy
79762-0000, TX Odessa
Phone: 432-366-0008
Fax: 432-366-6045

Packaging

Carton	1
Weight Per each	120

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed, NEC 230.62 (C) Compliant Barrier