



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DK3400 Type DK BRKR 3P 400A 240VAC Max 65KAIC @ 240V

Eaton Corp

Catalog Number	DK3400
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, K-Frame, DK, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 400 A, 240 Vac, 250 VDC, 65 Kaic At 240 Vac, 10 Kaic At 250 VDC, Aluminum, Line and Load, 50/60 HZ
Weight per unit	13.2 (lbs/each)
Product Category	3 Pole

Features

Current Rating	400 A
dimensions	14.0000 IN X 7.0000 IN X 6.5000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	240 Vac, 250 Vdc

Descriptions

Description	TYPE DK BRKR 3P 400A 240VAC MAX 65KAIC @ 240V
extra long description	ETN DK3400 DK BRK 3P 400A 240VAC MA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, K-frame, DK, Complete breaker, Fixed thermal, Fixed magnetic trip, Three-pole, 400 A, 240 Vac, 250 Vdc, 65 kAIC at 240 Vac, 10 kAIC at 250 Vdc, Aluminum, Line and load, 50/60 Hz
Product Type	DK BRK 3P 400A 240VAC Max 65KAIC @ 240V

Manufacturer Information

Brand	Eaton
GTIN	00786679044155
Manufacturers Part Number	DK3400
UPC	786679044155

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 13.2

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Frequency Rating 50 to 60 Hz

standard UL Listed