



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DNF14250MC Pan-Term® DNF14-250M-C Lo Panduit Corporation

Catalog Number	DNF14250MC
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Male Tab Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In A Blue, Nylon Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 16-14 Awg (1.5-2.5 MM ²). It Is 0.90" (22.9 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Standard Barrel Configuration and An Insulation Grip Sleeve Barrel. It Comes In Bottles Of 100.
Weight per unit	0.3000 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	#14

Material, Color, and Finish

Color	Blue
Finish	Nickel-Plated

Descriptions

Description	PAN-TERM® DNF14-250M-C LO
extra long description	PAN DNF14-250M-C Pan-Term® DNF14-25
Long Description	The vibration resistant male tab disconnect is made of copper and is nickel-plated. It is barrel insulated in a blue, nylon housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 16-14 AWG (1.5-2.5 mm ²). It is 0.90" (22.9 mm) long and 0.25" (6.4 mm) wide. The disconnect has a standard barrel configuration and an insulation grip sleeve barrel. It comes in bottles of 100.
Product Type	Pan-Term® DNF14-250M-C Loose Piece Disconnect

Manufacturer Information

Brand	Panduit®
GTIN	00074983827183
Manufacturers Part Number	DNF14-250M-C
UPC	074983827183



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

Packaging

Carton	100
Package	1000
Weight Per each	0.3

Uses, Certifications, and Standards

Mounting	1932-09-01
standard	UL 310 Listed, UL Listed 20H3 E78522; CSA Certified LR31212, C22.2 No.153
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)