



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DR10250L Disconnect *Panduit Corporation*

Catalog Number	DR10250L
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Female Disconnect Is Made Of Brass and Is Tin-Plated. It Is Non-Insulated In Metallic Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 12-10 Awg (4.0-6.0 MM ²). It Is 0.61" (15.5 MM) Long and 0.3" (7.6 MM) Wide. The Disconnect Has A Standard Barrel Configuration and A Sleeved Barrel. It Comes In Bottles Of 50.
Weight per unit	1.0 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Non-Insulated
Material	Brass
Voltage Rating	600
Wire Size	#10

Material, Color, and Finish

Finish	Tin-Plated
--------	------------

Descriptions

Description	DISCONNECT
extra long description	PAN DR10-250-L Pan-Term® DR10-250-L
Long Description	The vibration resistant female disconnect is made of brass and is tin-plated. It is non-insulated in metallic housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 12-10 AWG (4.0-6.0 mm ²). It is 0.61" (15.5 mm) long and 0.3" (7.6 mm) wide. The disconnect has a standard barrel configuration and a sleeved barrel. It comes in bottles of 50.
Product Type	Pan-Term® DR10-250-L Loose Piece Disconnect

Manufacturer Information

Brand	PANDUIT
GTIN	00074983827367
Manufacturers Part Number	DR10-250-L
UPC	074983827367



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

Packaging

Carton	50
Weight Per each	1

Uses, Certifications, and Standards

Mounting	1932-09-01
standard	UL 310 Listed, UL Listed 20H3 E78522; CSA Certified LR31212, C22.2 No.153
Temperature Rating	302 Degrees Fahrenheit (150 Degrees Celsius)