



DSD921 PB CNTRL Sta 2 CKT

Crouse-Hinds

Catalog Number	DSD921
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series DSD Front Operated Pushbutton Cover and Device Sub-Assembly, 10A, Black, Feraloy Iron Alloy, 2 Circuits Universal, 2 Buttons, Factory Sealed, 600 Vac
Weight per unit	4.0 (lbs/each)
Product Category	Control Station Cover Assemblies

Features

amperage rating	10
dimensions	5.3000 IN X 6.7000 IN X 4.6000 IN
Voltage Rating	600 VAC

Descriptions

Description	PB CNTRL STA 2 CKT
extra long description	CRS-H DSD921 DSD COVER AND DEVICE S
Features	New DSDX series available with NEMA 4X protection for Class I, Division 2 hazardous areas. Crouse-Hinds series DSD and DSDX explosionproof cover and device sub-assemblies are for use with our EDS/EDSC back boxes and EDSCM modular multi-gang device bodies. DSD/DSDX covers are available with a wide variety of devices and configurations, including manual motor starters, front operated pushbuttons, general use snap switches, side operated pushbuttons, selector switches and pilot lights. Certified for use in CI
Long Description	Eaton Crouse-Hinds series DSD front operated pushbutton cover and device sub-assembly, 10A, Black, Feraloy iron alloy, 2 circuits universal, 2 buttons, Factory sealed, 600 Vac
Product Type	DSD Cover and Device Sub Assemblies
Special Features	Factory sealed

Manufacturer Information

Brand	Eaton
GTIN	00782274576176
Manufacturers Part Number	DSD921
Model	Front operated pushbutton cover and device sub-assembly
UPC	782274576176

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION MOTOR CONTROL
----------------------	----------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.95

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III, NEMA 3/7B/7C/7D/9E/9F/9G
standard	UL 1203, CSA C22.2