



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700



E50KL355 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL355
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Lever, Rotary Lever, 1.5 Inch Len, Stainless Steel, Metal Roller 0.75 Inch Diameter 0.32 Inch Width, 14-250F(-10-121C), Stainless Steel, Steel, Ul, Csa, Ce
Weight per unit	0.1500 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

Features

actuator	Standard roller
dimensions	2.2200 IN X 0.7500 IN X 0.6500 IN

Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL355 E50 OPERATING LEVER
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Lever,Rotary lever,1.5 inch len,Stainless steel,Metal roller 0.75 inch diameter 0.32 inch width,14-250F(-10-121C),Stainless Steel,Steel, UL,CSA,CE
Product Type	E50 Operating Lever

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113297880
Manufacturers Part Number	E50KL355
UPC	782113297880

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory

Packaging

Carton	1
Weight Per each	0.15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	CE, CSA Certified, UL Listed, RoHS Compliant, CE Marked