



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVRFPKG1SWH Smart Switch & Remote Kit *Lutron*

Catalog Number	DVRFPKG1SWH
Manufacturer	Lutron
Description	Lut DVRF-PKG1S-WH Pico Paddle Remot
Weight per unit	0.6200 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	5
connection	Wireless
Connection Type	Wireless
load	5
Material	Thermoplastic
Mounting Type	Flat on Wall or over existing wallbox
operating cycles	3
Poles	1
Voltage Rating	120 V
Wattage	600

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Height	1.46
Length	2.96;75
Size	2.96 x .41 x 1.46
Width	0.41

Descriptions

Description	SMART SWITCH & REMOTE KIT
Features	Introducing the Claro smart switch for the Caseta smart lighting system. Lutron's most popular switch design is now smart and works with your existing Caseta products. Match existing paddle-style switches in your home with the same elegant, recognized aesthetic on both the switch and the Pico paddle remote. The Claro smart switch works with 5A LED lights or 3A fans; neutral wire required for operation. The Claro smart switch is ideal for areas where dimming is not needed, such as garages, hallways, or ou
Long Description	LUT DVRF-PKG1S-WH PICO PADDLE REMOT
Product Type	Pico Paddle Remote W Claro



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276816960
Manufacturers Part Number	DVRF-PKG1S-WH
UPC	784276816960

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Diva smart dimmer and Pico paddle remote

Packaging

Carton	1
Weight Per each	0.62

Uses, Certifications, and Standards

environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	431;437
Operating Temperature	32;140
standard	UL, CSA, NOM